

Datenblatt



Empfehlungen für Einbau und Abreinigung von ULTRATOP Filterpatronen															
Ø mm	L mm	FF m ²	Ab- rein.	Patronen/Ventil				Luftdruck bar	Luftmenge Normliter	On-time sek.	Venturi		Blasrohr		
				¾"	1,0"	1,5"	2,0"				höhe	Ø	Loch	abstan- d	
150	600	2,2	Jet	5	9	xxx	xxx	4,5-5,0	3 - 6	0,1-0,3	110	105	9	65	
	1000	3,6	Jet	3	5	9	xxx	4,5-5,0	5 - 10	0,1-0,3	110	105	9	65	
	1200	4,3	Jet	2	3	7	xxx	4,5-5,0	6 - 12	0,1-0,3	110	105	9	65	
	1400	5	Jet	2	3	6	xxx	4,5-5,0	7 - 14	0,1-0,3	110	105	9	65	
225	600	3	Jet	3	5	9	xxx	5,0-5,5	4 - 9	0,1-0,3	160	150	12	100	
	1000	5	Jet	2	4	6	xxx	5,0-5,5	7 - 15	0,1-0,3	160	150	12	100	
	1200	6	Jet	1	2	4	6	5,0-5,5	8 - 18	0,1-0,3	160	150	12	100	
	1400	7	Jet	1	2	3	5	5,0-5,5	10- 21	0,1-0,3	160	150	12	100	
325	600	7,8	Jet	1	2	3	4	5,5-6,0	12 - 25	0,1-0,3	160	210	16	120	
			RSD	1	2	xxx	xxx	3,5-4,0	40 - 50	0,5-4,0	xxx	xxx	xxx	xxx	
	1000	13	RSD	1	2	xxx	xxx	3,5-4,0	65 - 80	0,5-4,0	xxx	xxx	xxx	xxx	
			Jet	xxx	1	2	3	5,5-6,0	20 - 35	0,1-0,3	160	210	16	120	
	1200	15,6	RSD	1	2	xxx	xxx	3,5-4,0	80 - 100	0,5-4,0	xxx	xxx	xxx	xxx	
			Jet	xxx	1	2	3	5,5-6,0	25 - 45	0,1-0,3	160	210	16	120	
	1400	18,2	Jet	xxx	1	2	3	5,5-6,0	30 - 50	0,1-0,3	160	210	16	120	

- Schutzvermerk nach ISO 16016 – Protection notice as per ISO 16016 -